

[Home](#) ■ [Products](#) ■ [Screens and Fine Screens](#) ■ [STEP SCREEN®s](#)

STEP SCREEN®s



Cost-effective separation and transport of screenings

- for high separation efficiencies
- for any flow rate
- with optional lifting of screenings at bottom level

The success and broad acceptance of the STEP SCREEN® system is due to its function, the easy-to-understand operation method, the simple cleaning method without any aids (self-cleaning effect according to the counter current principle), easy servicing, its ability to handle very large screenings volumes and its operating reliability.

Contacting us means speaking with a partner who has more than 30 years experience with screens, their layout, construction, manufacture, operation and after-sales service and with more than 50,000 references worldwide is the unrivalled market leader in mechanical preliminary wastewater treatment.


- [HUBER Fine Screen STEP SCREEN® SSV](#)
- [HUBER Fine Screen STEP SCREEN® SSF](#)

Downloads


 [Brochure: STEP SCREEN® Vertical SSV](#) [pdf, 388 KB]

Further information


Design Sketch



Phase 1: The arriving screenings collect on the steps and form a carpet.



Phase 2 + 3: The complete screenings carpet is lifted and transported by rotation of the moveable laminae.



Phase 4: The screenings carpet is laid down on the next step above.

Benefits

- Lifting of screenings at bottom level due to a special bottom step design
- Gentle and complete screenings transport due to the counter-current principle
- Optimally adjustable to individual constructional conditions
- High capacity; the flow passes the screen surface only once
- High separation efficiency due to the narrow slot width and the produced screenings carpet
- Self-cleaning effect due to movable lamellas (no spray water, no brushes)
- Very high operational stability: Reduced susceptibility to grit, gravel and stones due to the bottom step washing system
- Very good corrosion protection: manufactured from stainless steel and acidtreated in a pickling bath
- Unrivalled experience for more than 20 years

Adresse / address: HUBER SE - Industriepark Erasbach A1 · 92334 Berching · Germany · Telefon / phone: + 49 - 84 62 - 201 - 0 · Fax / fax: + 49 - 84 62 - 201 - 810
e-mail: info@huber.de · Internet: http://www.huber.de

Sitz der Gesellschaft / Headquarters: Berching · AG Nürnberg / Register of companies: HRB 25558
Vorstand / Board: Georg Huber (Vorsitzender / CEO), Dr.-Ing. Oliver Rong (stellvertretender Vorsitzender / Vice CEO), Dr.-Ing. Johann Grienberger, Rainer Köhler
Aufsichtsratsvorsitzender / Chairman of the Supervisory Board: Alois Ponnath

USt (VAT)-IdNr.: DE 812353219

Bank: HypoVereinsbank Nürnberg (BLZ 760 200 70) 5 008 409 · SWIFT-BIC: HYVEDEMM460 · IBAN: DE 30 7602 0070 0005 0084 09

